

**QUICK GUIDE**

**DAB**  
WATER TECHNOLOGY

**DAB PUMPS LTD.**  
Units 4 and 5, Stortford Hall Industrial Park, Dunmow Road, Bishops Stortford, Herts CM23 5EZ - UK salesuk@dwgroup.com Tel: +44 1279 652 776 Fax: +44 1279 57 727

**DAB PUMPS IBERICA S.L.** Avenida de Castilla nr.1 Local 14 28830 - San Fernando De Henares - Madrid Spain info.spain@dwgroup.com Ph: +34 91 6569545 Fax: +34 91 6569676

**DAB PUMPS B.V.** Brusselstraat 150 B-1702 Groot-Bijgaarden - Belgium info.belgium@dwgroup.com Tel: +32 2 4668353 Fax: +32 2 4669218

**DAB PUMPS B.V.** Albert Einsteinweg, 4 5151 DL Drunen - Nederland info.nl@dwgroup.com Tel: +31 416 387280 Fax: +31 416 387299

**DAB PUMPS INC.** 3226 Benchmark Drive Ladson, SC 29456 USA info.usa@dwgroup.com Ph: 1-843-824-6332 Toll Free: 1-866-896-4DAB (4322) Fax: 1-843-797-3366

**DWT South Africa** Podium at Menlyn, 3rd Floor, Unit 3001b, 43 Ingersol Road, C/O Lois and Atterbury, Menlyn, Pretoria, 0181 South-Africa info.sa@dwgroup.com Tel: +27 12 361 3997 Fax: +27 12 361 3137

**ООО DAB PUMPS** Novgorodskaya str, 1, bld G, office 308 127247 Moscow - Russia info.dwtr@dwgroup.com Tel: +7 495 122 00 35 Fax: +7 495 122 00 36

**DAB PUMPEN DEUTSCHLAND GmbH** Tackweg 110 - 47918 Tönisvorst - Germany info.germany@dwgroup.com Tel: +49 2151 82136-0 Fax: +49 2151 82136-36

**DAB PUMPS POLAND SP. Z O.O.** Mokotów Marynarska ul. Postępu 15C 02-676 Warszawa - Poland Tel: +48 223 81 6065

**DAB UKRAINE Representative Office** Regus Horizon Park 4M, Hrinchenka St, suit 147 03680 Kiev, UKRAINE info.ukraine@dwgroup.com Tel: +38 044 391 59 43

**DAB PUMPS CHINA** No.40 Kaituo Road, Qingdao Economic & Technological Development Zone Qingdao City, Shandong Province, China PC: 266500 info.china@dwgroup.com Tel: +8653286812030-6270 Fax: +8653286812210



**DAB PRODUCTION HUNGARY KFT.** H-8800 Nagykánizsa, Buda Ernő u.5 Hungary Tel: +36.93501700

**DAB PUMPS DE MÉXICO, S.A. DE C.V.** Av Gral Alvaro Obregón 270, oficina 355 Hipódromo, Cuauhtémoc 06100 México, D.F. Tel: +52 55 6719 0493

**DAB**  
WATER TECHNOLOGY

**DAB PUMPS S.p.A.**  
Via M. Polo, 14 - 35035 Mezzano (PD) - Italy  
Tel: +39 049 5125000 - Fax: +39 049 5125950  
www.dabpumps.com

03/17 cod. 60182275



**Incorrect Installation:** A red 'X' is shown next to a faucet icon. The DAB control panel displays 'FAULT: BL Dry run' and '0,0 bar' and '0,10 kW'.

**Correct Installation:** A green 'Y' is shown next to a faucet icon. The DAB control panel displays 'GO' and '1,24 kW' and '2000 rpm' and '3,0 bar'.

**Control Panel Instructions:** A worker is shown holding a red hose. The DAB control panel displays 'Fill the pump' and 'Escape' and 'First priming'. A gauge shows a maximum depth of 5 feet.

### CONTRAST

3'' → 3'''

SET + [Down Arrow]

### LANGUAGE

MODE x3

### BACKLIGHT

MODE x3

### SET POINT

USER MENU			
STATE: GO	RS	2000 rpm	
VP	3,0 bar	VF	90,0 l/min
PO	1,40 kW	C1	4,8 Arms

3'' → MODE + SET =

SETPOINT MENU			
SP	Setpoint pressure		
	<b>3,0 bar</b>		
GO	2000 rpm	3,0 bar	

### PUMP ENABLE / DISABLE







[Up Arrow] + [Down Arrow]

### ANTICYCLING

TECH. ASS. MPAU	
AY	Anti cycling
	0 Disabled
GO	2000 rpm 3,0 bar

MODE + SET + [Up Arrow]

START → STOP → START (with warning)



1. Connect to the bottom of the tank.

2. Tighten the connection with a screwdriver.

3. Tighten the connection with pliers.

4. Tighten the connection with a screwdriver.

40°C Max

4°C Min

50°C Max (Warning)

0°C Min (Warning)

www.dabpumps.com